



G4753

connection line Wago 3x2,5² L=0,75m

Product Datasheet

Architecture

Connection system	Wago Winsta
-------------------	-------------

Connectivity

Number of wires	3
-----------------	---

Main electrical features

Nominal voltage	230 V
-----------------	-------

Electric current

Rated current	20 A
---------------	------

Length

Total length	0,75 m
--------------	--------

Power

Fire load	2638 kJ
-----------	---------

Resistance

Continuity resistor	1330 $\mu\Omega$
---------------------	------------------

Materials

Colour	black
--------	-------

Colour coding / contact insert	black
--------------------------------	-------

Colour housing	black
----------------	-------

Colour outer sheath	Black
---------------------	-------

Material	Mixed materials
----------	-----------------

Material group	mixed material
----------------	----------------

Type of surface treatment	coated
---------------------------	--------

Dimensions

Length	750 mm
--------	--------

Connection

Cross section connection cable	2,5 mm ²
--------------------------------	---------------------

Type of finished cable	Connecting cable
------------------------	------------------

Cable

Wire cross-section	2,5 mm ²
--------------------	---------------------

Cable permanent temperature-resistant to	70 °C
--	-------

Cable diameter	13 mm
----------------	-------

Conductor cross-section	2,5 mm ²
-------------------------	---------------------

Equipment

Type side 1	Bus
Mechanical coding	yes
Type side 2	Plug

Standards

European directive RoHs	voluntary compliance
-------------------------	----------------------

Safety

Protection index IP	IP20
Halogen free	no

temperatur

Insulating piece permanent temperature-resistant	105 °C
--	--------