



G4731

**Connection 2000mm, Schuko-angle-plug**

Product Datasheet

**Architecture**

Connection system Wago Winsta

**Connectivity**

Number of wires 3

**Main electrical features**

Nominal voltage 230 V

**Electric current**

Rated current 16 A

**Length**

Total length 2 m

**Power**

Fire load 5510 kJ

**Resistance**

Continuity resistor 1000  $\mu\Omega$

**Materials**

Colour black

Colour coding / contact insert black

Colour housing black

Colour outer sheath Black

Material group other

Type of surface treatment coated

**Dimensions**

Length 2000 mm

**Connection**

Cross section connection cable 1,5 mm<sup>2</sup>

Type of finished cable Device connection cable

**Cable**

Wire cross-section 1,5 mm<sup>2</sup>

Cable permanent temperature-resistant to 70 °C

Cable diameter 11 mm

Conductor cross-section 1,5 mm<sup>2</sup>

## Equipment

|                   |            |
|-------------------|------------|
| Type side 1       | Bus        |
| Mechanical coding | yes        |
| Type side 2       | Mains plug |

## Standards

|                         |                      |
|-------------------------|----------------------|
| European directive RoHs | voluntary compliance |
|-------------------------|----------------------|

## Safety

|                     |      |
|---------------------|------|
| Protection index IP | IP20 |
| Halogen free        | no   |

## temperatur

|                                                  |        |
|--------------------------------------------------|--------|
| Insulating piece permanent temperature-resistant | 105 °C |
|--------------------------------------------------|--------|