



G4751

Connection 4000mm, Schuko-angle-plug

Product Datasheet

Architecture

Connection system Wago Winsta

Connectivity

Number of wires 3

Main electrical features

Nominal voltage 230 V

Electric current

Rated current 16 A

Length

Total length 4 m

Power

Fire load 10130 kJ

Resistance

Continuity resistor 1000 $\mu\Omega$

Materials

Colour black

Colour coding / contact insert black

Colour housing black

Colour outer sheath Black

Material group other

Type of surface treatment coated

Dimensions

Length 4000 mm

Connection

Cross section connection cable 1,5 mm²

Type of finished cable Device connection cable

Cable

Wire cross-section 1,5 mm²

Cable permanent temperature-resistant to 70 °C

Cable diameter 11 mm

Conductor cross-section 1,5 mm²

Equipment

Type side 1	Bus
Mechanical coding	yes
Type side 2	Mains plug

Standards

European directive RoHs	voluntary compliance
-------------------------	----------------------

Safety

Protection index IP	IP20
Halogen free	no

temperatur

Insulating piece permanent temperature-resistant	105 °C
--	--------