



LF-trunking halogenfr. LFH 20x20mm white

Product Datasheet

Architecture

Fixing mode	bottom punched
-------------	----------------

Functions

Suitable for functional integrity according to DIN 4102-12	no
------------------------------------------------------------	----

Connectivity

Trunking coupling	without coupler
-------------------	-----------------

Capacity

Maximum number of cables (Ø 11 mm, 50% fill)	1
----------------------------------------------	---

Cover, door

Lid shape	premounted
-----------	------------

Materials

Colour	pure white
RAL colour	RAL 9010 - Pure white
Material	PC-ABS
Material group	plastic
Type of surface treatment	untreated
Transparent	no

Dimensions

Trunking height	18 mm
Length	2000 mm
Trunking width	19 mm
Distance bottom-punch along trunking-direction	125 mm

Cable

Internal/useful cross section	228 mm²
-------------------------------	---------

Scope of delivery

Delivery on roll	no
------------------	----

Equipment

Compartment quantity	1
Cable fixing clips included	yes
With protective film	no

Standards

Approvals	EN50085-2-1
European directive RoHs	voluntary compliance

LFH2002009010



Safety	
Halogen free	yes
temperatur	
Ambient temperature	-30...90 °C