



LFH3004509010



LF-trunking halogenfr. LFH 30x45mm white

Product Datasheet

Architecture

Fixing mode	bottom punched
-------------	----------------

Functions

Suitable for functional integrity according to DIN 4102-12	no
--	----

Configuration

Antibacterial treatment	no
-------------------------	----

Connectivity

Trunking coupling	Pre-equipped with couplers
-------------------	----------------------------

Capacity

Maximum number of cables (Ø 11 mm, 50% fill)	5
--	---

Cover, door

Lid shape	loose
-----------	-------

Materials

Colour	pure white
RAL colour	RAL 9010 - Pure white
Material	PC-ABS
Material group	plastic
Type of surface treatment	untreated
Transparent	no

Dimensions

Trunking height	30 mm
Length	2000 mm
Trunking width	45 mm
Distance bottom-punch along trunking-direction	125 mm

Cable

Internal/useful cross section	1010 mm ²
-------------------------------	----------------------

Scope of delivery

Delivery on roll	no
------------------	----

Equipment

Compartment quantity	1
Cable fixing clips included	yes
With protective film	no

Standards

Approvals	EN50085-2-1
European directive RoHs	voluntary compliance

Safety

Protection index IP	IP30
Halogen free	yes
Impact strength	IK07

Use conditions

Operating temperature	-5...90 °C
-----------------------	------------

temperatur

Ambient temperature	-30...90 °C
---------------------	-------------