



T-piece, LFH 30045, pure white

Product Datasheet

#### Architecture

Fixing mode	Hold in position thanks to lid
-------------	--------------------------------

#### Functions

Overlapping	no
Suitable for functional integrity according to DIN 4102-12	no

#### Configuration

Symmetrical	yes
-------------	-----

#### Cover, door

Lid with softlip	-
------------------	---

#### Materials

Colour	pure white
RAL colour	RAL 9010 - Pure white
Material	PC-ABS
Material group	plastic
Type of surface treatment	untreated

#### Dimensions

Trunking height	30 mm
Trunking width	45 mm
Measure a	130 mm

#### Installation, mounting

Base punching	Without base punching
---------------	-----------------------

#### Accessories included

Accessory configuration	Moulded
-------------------------	---------

#### Equipment

With protective film	no
----------------------	----

#### Standards

European directive RoHs	voluntary compliance
-------------------------	----------------------

#### Safety

Halogen free	yes
--------------	-----

#### temperatur

Ambient temperature	-30...90 °C
---------------------	-------------

M66569010

