



WS122T



Systo 2-g socket 2P+T 16A screwless Alu

Product Datasheet

Architecture

Fixing mode Recessed

Functions

Overvoltage protection no

Controls and indicators

Indicator lamp no

With or without indicator without

Connectivity

With USB charging socket no

Main electrical features

Frequency 50/60 Hz

Nominal voltage 250 V

Cover, door

Interlockable no

Power supply

Special power supply No special power supply

Materials

RAL colour RAL 9006 - White aluminium

Material Polycarbonate (PC)

Surface appearance satin finish

Type of surface treatment Painted

Dimensions

Depth of installed product 42,5 mm

Height of installed product 45 mm

Width of installed product 90 mm

Dimensions (LLxwxh) 90x45x42.5

Installation, mounting

Fixing type Clipped

Connection

Phase pickup L1

Equipment

On/Off switch no

Standards

Approvals	NFC 61314
-----------	-----------

Safety

Protection index IP	21D
IK protection code against mechanical impacts	07

Identification

Range	systo
-------	-------
