

# Cartouches-fusibles



LF300G

**Type gG**

Description	Pack	Art No.
Cartouche fus.10x38 gG 0.5A	10	<b>LF300G</b>
Cartouche fus.10x38 gG 1A	10	<b>LF301G</b>
Cartouche fus.10x38 gG 2A	10	<b>LF302G</b>
Cartouche fus.10x38 gG 4A	10	<b>LF304G</b>
Cartouche fus.10x38 gG 6A	10	<b>LF306G</b>
Cartouche fus.10x38 gG 8A	10	<b>LF308G</b>
Cartouche fus.10x38 gG 10A	10	<b>LF310G</b>
Cartouche fus.10x38 gG 12A	10	<b>LF312G</b>
Cartouche fus.10x38 gG 16A	10	<b>LF316G</b>
Cartouche fus.10x38 gG 20A	10	<b>LF320G</b>
Cartouche fus.10x38 gG 25A	10	<b>LF325G</b>
Cartouche fus.10x38 gG 32A	10	<b>LF332G</b>
Cartouche fus.14x51 gG 2A	10	<b>LF402G</b>
Cartouche fus.14x51 gG 4A	10	<b>LF404G</b>
Cartouche fus.14x51 gG 6A	10	<b>LF406G</b>
Cartouche fus.14x51 gG 8A	10	<b>LF408G</b>
Cartouche fus.14x51 gG 10A	10	<b>LF410G</b>
Cartouche fus.14x51 gG 12A	10	<b>LF412G</b>
Cartouche fus.14x51 gG 16A	10	<b>LF416G</b>
Cartouche fus.14x51 gG 20A	10	<b>LF420G</b>
Cartouche fus.14x51 gG 25A	10	<b>LF425G</b>
Cartouche fus.14x51 gG 32A	10	<b>LF432G</b>
Cartouche fus.14x51 gG 40A	10	<b>LF440G</b>
Cartouche-fusible indus 14x51 gG 45A	10	<b>LF445G</b>
Cartouche fus.14x51 gG 50A	10	<b>LF450G</b>
Cartouche fus.22x58 gG 16A	10	<b>LF516G</b>
Cartouche fus.22x58 gG 20A	10	<b>LF520G</b>
Cartouche fus.22x58 gG 25A	10	<b>LF525G</b>
Cartouche fus.22x58 gG 32A	10	<b>LF532G</b>
Cartouche fus.22x58 gG 40A	10	<b>LF540G</b>
Cartouche fus.22x58 gG 50A	10	<b>LF550G</b>
Cartouche fus.22x58 gG 63A	10	<b>LF563G</b>
Cartouche fus.22x58 gG 80A	10	<b>LF580G</b>
Cartouche fus.22x58 gG 100A	10	<b>LF590G</b>
Cartouche fus.22x58 gG 125A	10	<b>LF599G</b>



LF300M

## Type aM

Description	Pack	Art No.
Cartouche fus.10x38 aM 0.5A	10	<b>LF300M</b>
Cartouche fus.10x38 aM 1A	10	<b>LF301M</b>
Cartouche fus.10x38 aM 2A	10	<b>LF302M</b>
Cartouche fus.10x38 aM 4A	10	<b>LF304M</b>
Cartouche fus.10x38 aM 6A	10	<b>LF306M</b>
Cartouche fus.10x38 aM 8A	10	<b>LF308M</b>
Cartouche fus.10x38 aM 10A	10	<b>LF310M</b>
Cartouche fus.10x38 aM 12A	10	<b>LF312M</b>
Cartouche fus.10x38 aM 16A	10	<b>LF316M</b>
Cartouche fus.10x38 aM 20A	10	<b>LF320M</b>
Cartouche fus.10x38 aM 25A	10	<b>LF325M</b>
Cartouche-fusible indus 10x38 aM 32A	10	<b>LF332M</b>
Cartouche fus.14x51 aM 2A	10	<b>LF402M</b>
Cartouche fus.14x51 aM 4A	10	<b>LF404M</b>
Cartouche fus.14x51 aM 6A	10	<b>LF406M</b>
Cartouche fus.14x51 aM 8A	10	<b>LF408M</b>
Cartouche fus.14x51 aM 10A	10	<b>LF410M</b>
Cartouche fus.14x51 aM 12A	10	<b>LF412M</b>
Cartouche fus.14x51 aM 16A	10	<b>LF416M</b>
Cartouche fus.14x51 aM 20A	10	<b>LF420M</b>
Cartouche fus.14x51 aM 25A	10	<b>LF425M</b>
Cartouche fus.14x51 aM 32A	10	<b>LF432M</b>
Cartouche fus.14x51 aM 40A	10	<b>LF440M</b>
Cartouche-fusible indus 14x51 aM 45A	10	<b>LF445M</b>
Cartouche fus.14x51 aM 50A	10	<b>LF450M</b>
Cartouche fus.22x58 aM 16A	10	<b>LF516M</b>
Cartouche fus.22x58 aM 20A	10	<b>LF520M</b>
Cartouche fus.22x58 aM 25A	10	<b>LF525M</b>
Cartouche fus.22x58 aM 32A	10	<b>LF532M</b>
Cartouche fus.22x58 aM 40A	10	<b>LF540M</b>
Cartouche fus.22x58 aM 50A	10	<b>LF550M</b>
Cartouche fus.22x58 aM 63A	10	<b>LF563M</b>
Cartouche fus.22x58 aM 80A	10	<b>LF580M</b>
Cartouche fus.22x58 aM 100A	10	<b>LF590M</b>
Cartouche fus.22x58 aM 125A	10	<b>LF599M</b>