

vega D

The vega D enclosure is adapted for installations in houses and commercial premises up to 160 A. It can be delivered in a ready-to-mount configuration or to be completed. All the enclosures of this range have 24 modules rows.

**Insertion part**

Description	Pack	Art No.
Cable entry plate, NewVegaD, w. 2x flange	Qty. 1	FD00P2

FD00P2

**Blankings**


Description	Pack	Art No.
Cover strips, universal, for 1/2 module	50	P031F
Cover strips, universal, for 1 module	50	P032F
Cover strip, universal, 24M, RAL 9010	10	JP002

P031F

**Adaptor**


Description	Pack	Art No.
Adaptor, universN, double, 20pcs	Qty. 1	UZ01V1

UZ01V1

**Horizontal trunking**

Description	Pack	Art No.
Slotted trunking 80x30 grey NewVegaD	Qty. 1	FD00T1
Slot. trunking, NewVegaD, 80x30mm, lightgr.	1	FD00T2

FD00T1

**diagram holder**

Description	Pack	Art No.
Document holder, T, DIN A4	10	FZ794

FZ794