

Main incomers

H3 MCCBs references guide



	Trip unit	In	Nbr of poles	MCCBs				Trip free switches	Add-on block	Base plate for plug-in MCCBs	Accessories for draw-out and plug-in MCCBs			Collar terminals		Extended connection		Inter-phase barriers					
				25kA adj./adj.	50kA adj./adj.	65kA adj./adj.	70kA adj./adj.				Auxiliary terminal 5 wires panel side	Auxiliary terminal 3 wires body side	Auxiliary terminal 2 wires body side	Simple Copper Alu	Double Alu	Straight	Spreader						
h250	TM	20A	3P-3d	HHG020U	HNG020U									HYC003H	HYB005H	HYC010H	HYC011H	HYB019H					
			4P-3dNr		HNG021U								HYC004H	HYB006H						HYB012H			
		32A	3P-3d	HHG032U	HNG032U														HYC003H	HYB005H			HYC011H
			4P-3dNr		HNG033U														HYC004H	HYB006H			HYB012H
		63A	3P-3d	HHG063U	HNG063U	HEG063U													HYC003H	HYB005H			HYC011H
			4P-3dNr		HNG064U	HEG064U													HYC004H	HYB006H			HYB012H
		100A	3P-3d	HHG100U	HNG100U	HEG100U													HYC003H	HYB005H			HYC011H
			4P-3dNr		HNG101U	HEG101U													HYC004H	HYB006H			HYB012H
		125A	3P-3d	HHG125U	HNG125U	HEG125U													HYC003H	HYB005H			HYC011H
			4P-3dNr		HNG126U	HEG126U													HYC004H	HYB006H			HYB012H
		160A	3P-3d	HHG160U	HNG160U	HEG160U													HYC003H	HYB005H			HYC011H
			4P-3dNr		HNG161U	HEG161U													HYC004H	HYB006H			HYB012H
	200A	3P-3d	HHG200U	HNG200U	HEG200U										HYC003H	HYB005H			HYC011H				
		4P-3dNr		HNG201U	HEG201U										HYC004H	HYB006H			HYB012H				
	250A	3P-3d	HHG250U	HNG250U	HEG250U										HYC003H	HYB005H			HYC011H				
		4P-3dNr		HNG251U	HEG251U										HYC004H	HYB006H			HYB012H				
	LSI	40A	3P-3d		HNC040H		HEC040H								HYC003H	HYB005H			HYC011H				
			4P-3dNr		HNC041H		HEC041H									HYC004H	HYB006H			HYB012H			
		125A	3P-3d		HNC125H		HEC125H								HYC003H	HYB005H			HYC011H				
			4P-3dNr		HNC126H		HEC126H									HYC004H	HYB006H			HYB012H			
	250A	3P-3d		HNC250H		HEC250H									HYC003H	HYB005H			HYC011H				
		4P-3dNr		HNC251H		HEC251H									HYC004H	HYB006H			HYB012H				
	Plug-in	40A	3P-3d		HNC040G				HYC200H	HYC250H	HYC353H	HYC352H											
			4P-3dNr		HNC041G				HYC201H														
125A		3P-3d		HNC125G				HYC200H															
		4P-3dNr		HNC126G				HYC201H															
250A	3P-3d		HNC250G				HYC200H																
	4P-3dNr		HNC251G				HYC201H																
h630	TM	250A	3P-3d	HHD250U	HND250U									HYD003H	HYD005H	HYD007H	HYD010H	HYD011H	HYD019H				
			4P-3dNr		HND251U										HYD004H	HYD006H				HYD008H	HYD012H		
		400A	3P-3d	HHD400U	HND400U										HYD003H	HYD005H				HYD007H		HYD011H	HYD019H
			4P-3dNr		HND401U										HYD004H	HYD006H				HYD008H		HYD012H	HYD019H
	LSI	250A	3P-3d												HYD003H	HYD005H	HYD007H		HYD011H	HYD019H			
			4P-3dNr					HBD401H							HYD004H	HYD006H	HYD008H		HYD012H	HYD019H			
		400A	3P-3d		HND400H	HED400H	HCD400U								HYD003H	HYD005H	HYD007H		HYD011H	HYD019H			
			4P-3dNr		HND401H	HED401H	HCD401U	HBD401H							HYD004H	HYD006H	HYD008H		HYD012H	HYD019H			
	630A	3P-3d		HND630H	HED630H	HCD630U									HYD005H	HYD007H	HYD013H		HYD014H	HYD019H			
		4P-3dNr		HND631H	HED631H	HCD631U	HBD631H/500A								HYD006H	HYD008H			HYD015H	HYD019H			
	Plug-in	250A	3P-3d			HED250G			HYD200H	HYC250H	HYC353H	HYC352H											
			4P-3dNr			HED251G			HYD201H														
400A	3P-3d				HED400G			HYD200H															
	4P-3dNr				HED401G			HYD201H															
h1000	LSI	800A	3P-3d		HNE800H	HEE800H	HCE800U									HYE007H	included	HYD019H					
			4P-3dNr		HNE801H	HEE801H	HCE801U								HYE008H				HYD019H				
		1000A	3P-3d		HNE970H	HEE970H	HCE970U														HYD019H		
			4P-3dNr		HNE971H	HEE971H	HCE971U														HYD019H		
	Plug-in	630A	3P-3d			HEE630G			HYE200H	HYC250H	HYC353H	HYC352H											
			4P-3dNr			HEE631G			HYE201H														
		800A	3P-3d			HEE800G			HYE200H														
			4P-3dNr			HEE801G			HYE201H														
h1600	LSI	1250A	3P-3d		HNF980H	HEF980H	HCF980U										included	HYD019H					
			4P-3dNr		HNF981H	HEF981H	HCF981U												HYD019H				
		1600A	3P-3d		HNF990H	HEF990H	HCF990U													HYD019H			
			4P-3dNr		HNF991H	HEF991H	HCF991U													HYD019H			

h250 - h630 - h1000 - h1600	Range	Auxiliary contact 1NO + 1NC		Auxiliary alarm contact 1NO + 1NC		Auxiliary low level contact 1NO + 1NC		Auxiliary low level contact 1NO + 1NC
Auxiliary contact				HXC024H		HXC025H		HXC026H
Coil voltage		24V DC	48V DC	V AC 120 - 100	V DC 120 - 100	V AC 240 - 200	V DC 240 - 200	V AC 450 - 380
Shunt trip	h250 to h1000 h1600	HXC001H HXF001H	HXC002H HXF002H	HXC003H HXF003H	HXC008H HXF008H	HXC004H HXF004H		HXC005H HXF005H
Undervoltage release	h250 to h630 h1000 to h1600	HXC011H HXE011H		HXC013H HXE013H	HXC018H HXE018H	HXC014H HXE014H	HXC019H HXE019H	HXC015H HXE015H
Undervoltage release delayed	h250 h630 h1000 h1600	HXC051H HXD051H HXE051H HXF051H		HXC053H HXD053H HXE053H HXF053H		HXC054H HXD054H HXE054H HXF054H		HXC055H HXD055H HXE055H HXF055H

