



HXC018H

Undervolt. Release 100-120VDC(h250..630)

Product Datasheet

Voltage

Rated operational voltage in DC	110 V
---------------------------------	-------

Power

Inrush power absorbed	0,56 VA
-----------------------	---------

Total power loss under IN	1,2 W
---------------------------	-------

Connection

Type of connection	with screw
--------------------	------------

Standards

European directive WEEE	concerned
-------------------------	-----------

Safety

Protection index IP	IP4X
---------------------	------

Use conditions

Degree of pollution according to IEC 60664 / IEC 60947-2	3
--	---

Altitude	2000 m
----------	--------