



HXC019H

Undervolt. Release 200-240VDC(h250..630)

Product Datasheet

Voltage

Rated operational voltage in DC 24 V

Power

Inrush power absorbed 0,56 VA

Total power loss under IN 2,4 W

Connection

Type of connection with screw

Standards

European directive WEEE concerned

Safety

Protection index IP IP4X

Use conditions

Degree of pollution according to IEC 60664 / IEC 60947-2 3

Altitude 2000 m