



## UVR 200-240 V DC (h800-h1000-h1600)

HXE019H

### Functions

Delay off	no
-----------	----

### Voltage

Rated operational voltage in DC	24 V
---------------------------------	------

### Power

Inrush power absorbed	0,7 VA
Total power loss under IN	2,6 W

### Connection

type of connection	with screw
--------------------	------------

### Standards

European directive RoHS	voluntary compliance
European directive WEEE	concerned

### Safety

Protection index IP	IP4X
---------------------	------

### Use conditions

Degree of pollution according to IEC 60664 / IEC 60947-2	3
Altitude	2000 m