



WS012N



WS012N



Systo 1M 2W switch Black

Product Datasheet

Architecture

Type of order	Switch
Type of control unit	single rocker
Fixing mode	Recessed

Controls and indicators

Indicator lamp	no
----------------	----

Main electrical features

Frequency	50/60 Hz
Nominal voltage	250 V

Capacity

Number of modules for WA	1
--------------------------	---

Materials

RAL colour	RAL 8022 - Black brown
Colour	black
Material	Polycarbonate (PC)
Type of surface treatment	mat

Dimensions

Depth of installed product	33 mm
Height of installed product	45 mm
Width of installed product	22 mm
Dimensions (LLxwxhh)	22.5x45x33

Connection

Type of connection	quick connect
Type of contacts	2 way

Standards

Approvals	EN 60669-1
-----------	------------

Safety

Protection index IP	IP31D
IK protection code against mechanical impacts	07
Glow wire test	according to NFC-20455 : 960°C

Use conditions

Storage temperature	-10 to 50 °C
---------------------	--------------

Identification

Composition	Mechanism with upper casing
Range	system
