



VF312TJ



VF312TJ1

Sm.distr, golf, flush, 36M, transp. door

Technische Merkmale

Architecture

Fixing mode	flush-mounting
-------------	----------------

Functions

With a pipe-in lead	yes
---------------------	-----

Compatibility

Compatible with DIN rail mounting	yes
-----------------------------------	-----

Main electrical features

Nominal voltage	400 V
-----------------	-------

Electric current

Rated current	63 A
---------------	------

Cover, door

Type of door closing	Latch
Identification of protection index	40
Interlockable	no
Cover type	Closed (plain)
Door locking	without
Door leave	single
Door quantity	1
Cover type	Door
Transparent cover or door	yes

Materials

Colour	pure white
Colour	white
RAL colour	RAL 9010 - Pure white
Material	plastic
Type of surface treatment	untreated

Dimensions

Insertion depth	72 mm
Depth of wall niche	72 mm
Depth of installed product	97,5 mm
Internal depth	97,5 mm
Height of installed product	543 mm
Installation height	507 mm
Width of installed product	352 mm
Width in division units	12
Built-in height	507 mm
Built-in width	318 mm

Installation, mounting

Suitable for outdoor use	no
--------------------------	----

Accessories included

Mounting plate included	no
With lock	no

Equipment

Number of rows	3
Quantity of section in width	1
Quantity of rails	3
Can be accessorized	yes
Extension possible	yes

Standards

GWT Glow wire test	650 °C
European directive WEEE	concerned

Safety

IK protection code against mechanical impacts	IK07
Protection index IP	IP40
Protection class	isol.class II
Halogen free	yes
Ultraviolet resistant	no

Use conditions

Operating temperature	-25...40 °C
-----------------------	-------------