



VZ016M

Cable gland, vector, IP65, M16

Technische Merkmale

Architecture

Thread type	Metric
-------------	--------

Compatibility

Suitable for nominal thread metric/PG	0/16
---------------------------------------	------

Materials

Colour	light grey
Material	plastic
Type of surface treatment	untreated

Dimensions

Screw head size in mm	22 mm
thread gradient	1,5

Connection

Clamping range	5 - 10 mm
----------------	-----------

Equipment

Screened	no
----------	----

Standards

European directive WEEE	not concerned
-------------------------	---------------

Safety

Safe use in explosive atmosphere	no
Protection index IP	IP65
Halogen free	yes
Compliant Ex-Zone dust	none
For Ex-zone gas	no

Use conditions

Operating temperature	-25 ... 40 °C
-----------------------	---------------