



VE103L

Encl., vector, IP5x, 3M, version AUT

#### Technische Merkmale

#### Architecture

Fixing mode	surface-mounting
-------------	------------------

#### Functions

With a pipe-in lead	yes
---------------------	-----

#### Compatibility

Compatible with DIN rail mounting	yes
-----------------------------------	-----

#### Main electrical features

Nominal voltage	400 V
-----------------	-------

#### Electric current

Rated current	63 A
---------------	------

#### Cover, door

Type of door closing	Latch
Identification of protection index	65
Interlockable	no
Cover type	Closed (plain)
Door locking	without
Door leave	single
Door quantity	1
Cover type	Door
Transparent cover or door	yes

#### Materials

Colour	light grey
Colour	light grey
RAL colour	RAL 7035 - Light grey
Material	Polystyrol (PS)
Type of surface treatment	untreated

#### Dimensions

Depth of installed product	93 mm
Internal depth	93 mm
Height of installed product	175 mm
Width of installed product	111 mm
Width in division units	3
Thickness of sidewall material	2,5 mm

#### Installation, mounting

Suitable for outdoor use	yes
--------------------------	-----

## Connection

Number of conduit inlets	2
--------------------------	---

## Accessories included

Mounting plate included	no
With lock	no

## Equipment

Number of rows	1
Quantity of section in width	1
Quantity of rails	1
Can be accessorized	yes
Number of openings for flange plates	6
Extension possible	no

## Standards

GWT Glow wire test	750 °C
European directive WEEE	concerned

## Safety

IK protection code against mechanical impacts	IK07
Protection index IP	IP65
Protection class	isol.class II
Halogen free	yes
Ultraviolet resistant	no

## Use conditions

Operating temperature	-25...40 °C
-----------------------	-------------