



TN204S

TV/SAT SPLITTER 4 WAYS (DIN RAIL CLIP)

Technische Merkmale

Architecture

Fixing mode Din-Rail or on a fixing plate

Connectivity

Input(s) 1

Frequency

Frequency band 5/2400 MHz

Dimensions

Dimensions (LLxwxhh) 75 x 35 x 27 mm

Connection

Type of connection terminal standard "F" for coaxial cable

Equipment

Number of outputs 4

Number of branches 4

Use

Attenuation 3,7 to 7 dB