



LFF600967030



**End cap for LFF60090 and LFF40090 gr**

Technische Merkmale

**Architecture**

Fixing mode	Clamping and screwable
-------------	------------------------

**Functions**

Overlapping	yes
Suitable for functional integrity according to DIN 4102-12	no

**Configuration**

Antibacterial treatment	no
-------------------------	----

**Connectivity**

Trunking coupling	without coupler
-------------------	-----------------

**Materials**

Colour	stone grey
RAL colour	RAL 7030 - Stone grey
Material	PC-ABS
Material group	plastic
Type of surface treatment	untreated

**Dimensions**

Trunking height	60 mm
Trunking width	90 mm
Profile height	40-60 mm

**Equipment**

With protective film	no
----------------------	----

**Standards**

Approvals	EN50085-2-1
European directive RoHs	voluntary compliance

**Safety**

Halogen free	yes
Impact strength	IK07

**Use conditions**

Operating temperature	-5...60 °C
-----------------------	------------

**temperatur**

Ambient temperature	-5...60 °C
---------------------	------------