



VE112L

Encl., vectorII, IP5x, 12M, version AUT

Technische Merkmale

Architecture

Fixing mode surface-mounting

Functions

With a pipe-in lead yes

Compatibility

Compatible with DIN rail mounting yes

Main electrical features

Nominal voltage 400 V

Electric current

Rated current 63 A

Cover, door

Type of door closing Latch

Identification od protection index 65

Interlockable no

Cover type Closed (plain)

Door locking without

Door leave single

Door quantity 1

Cover type Door

Transparent cover or door yes

Materials

Colour light grey

Colour light grey

RAL colour RAL 7035 - Light grey

Material Polystyrol (PS)

Type of surface treatment untreated

Dimensions

Depth of installed product 151 mm

Internal depth 151 mm

Height of installed product 302 mm

Width of installed product 310 mm

Width in division units 12

Thickness of sidewall material 2,5 mm

Installation, mounting

Suitable for outdoor use yes

Connection

Number of conduit inlets	12
--------------------------	----

Accessories included

Mounting plate included	no
With lock	no

Equipment

Number of rows	1
Quantity of section in width	1
Quantity of rails	1
Can be accessorized	yes
Number of openings for flange plates	46
Extension possible	no

Standards

GWT Glow wire test	750 °C
European directive WEEE	concerned

Safety

IK protection code against mechanical impacts	IK08
Protection index IP	IP65
Protection class	isol.class II
Halogen free	yes
Ultraviolet resistant	no

Use conditions

Operating temperature	-25...40 °C
-----------------------	-------------