



VE118L

Encl., vector, IP5x, 18M, version AUT

Technische Merkmale

Architecture

Fixing mode surface-mounting

Functions

With a pipe-in lead yes

Compatibility

Compatible with DIN rail mounting yes

Main electrical features

Nominal voltage 400 V

Cover, door

Cover type Closed (plain)

Transparent cover or door yes

Cover type Door

Door locking without

Type of door closing Latch

Door leave single

Door quantity 1

Identification od protection index 55

Interlockable no

Materials

RAL colour RAL 7035 - Light grey

Colour light grey

Colour light grey

Material plastic

Enclosure material polystyrene

Type of surface treatment untreated

Dimensions

Depth of installed product 151 mm

Internal depth 151 mm

Height of installed product 302 mm

Width of installed product 418 mm

Width in division units 18

Thickness of sidewall material 2,5 mm

Installation, mounting

Suitable for outdoor use yes

Connection

Number of conduit inlets 15

Accessories included

Mounting plate included	no
With lock	no

Equipment

Number of openings for flange plates	46
Number of rows	1
Quantity of section in width	1
Can be accessorized	yes
Quantity of rails	1

Standards

GWT Glow wire test	750 °C
European directive WEEE	concerned

Safety

Protection class	isol.class II
Protection index IP	IP55
IK protection code against mechanical impacts	07
Halogen free	yes
Ultraviolet resistant	yes

Use conditions

Operating temperature	-25 ... 40 °C
-----------------------	---------------