



WRSS81PSW



IP20

1G DP SW SOCKET POLISHED STEEL WHITE

Technische Merkmale

Architecture

Fixing mode	flush-mounting
-------------	----------------

Functions

Overvoltage protection	no
------------------------	----

Main electrical features

Nominal voltage	250 V
Rated voltage	220...230 V AC
Rated current	13 A

Electric current

Rated current	13 A
---------------	------

Cover, door

Cover	Full cover plate
-------	------------------

Power supply

Special power supply	No special power supply
----------------------	-------------------------

Materials

Colour	silver optics
Material	stainless steel
Surface appearance	glossy
Type of surface treatment	Other

Dimensions

Depth	25,8 mm
Height	86 mm
Width	86 mm

Installation, mounting

Fixing type	With screws
Installation mode	for flush-mounted and hollow-wall mounting, for screw fastening

Connection

Type of connection	screw
--------------------	-------

Cable

- with earth connection

Scope of delivery

- with 2 fixing screws M3.5 x 30 mm

Equipment

Number of socket outlets switchable	1
-------------------------------------	---

Use

Differentiation characteristic 3 - Sales	with screw terminals
--	----------------------

Safety

IK protection code against mechanical impacts	sonstige
Protection index IP	IP20
- Enhanced contact protection	

Use conditions

Insert	insert white
--------	--------------