



Terminal, Volta, add.terminal, 3Ph+N, 63A

Technische Merkmale

Architecture

Number of poles	2 P
Fixing mode	Snap

Electric current

Rated current	63 A
---------------	------

Materials

Colour	pure white
Colour	white
RAL colour	RAL 9010 - Pure white
Material	Mixed materials
Transparent	no

Dimensions

Height of installed product	38 mm
Length	270 mm
Width of installed product	17 mm

Connection

Conductor cross-section (flexible), with wire end sleeve	1,5...25 mm ²
Conductor cross-section (flexible), without wire end sleeve	1,5...25 mm ²
Connection cross-section of input and output with screws, for massive conductors	1,5 / 25 mm ²
Connection cross section of access and exit with screws, for flexible conductor	8 / 15 mm ²
Type of connection	Quickconnect

Accessories included

Closing plate required	no
------------------------	----

Equipment

Number of clamp positions	16
---------------------------	----

Standards

European directive WEEE	concerned
-------------------------	-----------

Safety

Safe use in explosive atmosphere	no
----------------------------------	----

Use conditions

Operating temperature	-25...40 °C
-----------------------	-------------