



VZ603N

## Door, golf, white, VF/VS112

### Technische Merkmale

#### Architecture

Intended door position	left
Fixing mode	Clamping

#### Configuration

Version as door for disconnecting switch interlocking	no
---	----

#### Cover, door

Type of door closing	Latch
Door type for switch gear cabinet	Stop door
Door leave	single
Door quantity	1
With cut out	yes
Door included	yes
Transparent cover or door	no

#### Materials

Colour	RAL 9010
Colour	white
RAL colour	RAL 9010 - Pure white
Material	plastic
Surface appearance	glossy
Type of surface treatment	untreated

#### Dimensions

Depth of installed product	16,5 mm
Internal depth	16,5 mm
Height of installed product	250 mm
Width of installed product	280 mm
Built-in height	250 mm
Built-in width	280 mm

#### Installation, mounting

Suitable for outdoor use	no
--------------------------	----

#### Equipment

Number of rows	1
Quantity of section in width	1

#### Standards

European directive WEEE	not concerned
-------------------------	---------------

## Safety

IK protection code against mechanical impacts	IK07
Protection index IP	IP40
Protection class	isol.class II
Halogen free	yes
Ultraviolet resistant	no

## Use conditions

Operating temperature	-25...40 °C
-----------------------	-------------

## Shape

Slotted	no
---------	----