



VZ623N

Door, golf, transp., VF/VS112

Technische Merkmale

Architecture

Intended door position	left
Fixing mode	Clamping

Cover, door

Transparent cover or door	yes
Door type for switch gear cabinet	Stop door
Type of door closing	Latch
Door leave	single
Door quantity	1
Door included	yes

Materials

Colour	transparent
Material	plastic
Type of surface treatment	untreated

Dimensions

Depth of installed product	16,5 mm
Internal depth	16,5 mm
Height of installed product	250 mm
Built-in height	250 mm
Built-in width	280 mm
Width of installed product	280 mm

Equipment

Number of rows	1
Quantity of section in width	1

Standards

European directive WEEE	not concerned
-------------------------	---------------

Safety

Protection class	isol.class II
Protection index IP	IP40
IK protection code against mechanical impacts	IK07
Halogen free	yes
Ultraviolet resistant	no

Use conditions

Operating temperature	-25 ... 40 °C
-----------------------	---------------