



VZ624N

Door, golf, transp., VF/VS212

Technische Merkmale

Architecture

| | |
|------------------------|----------|
| Intended door position | left |
| Fixing mode | Clamping |

Configuration

| | |
|---|----|
| Version as door for disconnecting switch interlocking | no |
|---|----|

Cover, door

| | |
|-----------------------------------|-----------|
| Type of door closing | Latch |
| Door type for switch gear cabinet | Stop door |
| Door leave | single |
| Door quantity | 1 |
| With cut out | yes |
| Door included | yes |
| Transparent cover or door | yes |

Materials

| | |
|---------------------------|-------------|
| Colour | transparent |
| Colour | transparent |
| Material | plastic |
| Type of surface treatment | untreated |

Dimensions

| | |
|-----------------------------|---------|
| Depth of installed product | 16,5 mm |
| Internal depth | 16,5 mm |
| Height of installed product | 375 mm |
| Width of installed product | 280 mm |
| Built-in height | 375 mm |
| Built-in width | 280 mm |

Installation, mounting

| | |
|--------------------------|----|
| Suitable for outdoor use | no |
|--------------------------|----|

Equipment

| | |
|------------------------------|---|
| Number of rows | 2 |
| Quantity of section in width | 1 |

Standards

| | |
|-------------------------|---------------|
| European directive WEEE | not concerned |
|-------------------------|---------------|

Safety

| | |
|---|---------------|
| IK protection code against mechanical impacts | IK07 |
| Protection index IP | IP40 |
| Protection class | isol.class II |
| Halogen free | yes |
| Ultraviolet resistant | no |

Use conditions

| | |
|-----------------------|-------------|
| Operating temperature | -25...40 °C |
|-----------------------|-------------|

Shape

| | |
|---------|----|
| Slotted | no |
|---------|----|