



## Earth rail & brace quadro.sys. L250 mm

### Technische Merkmale

#### Architecture

Fixing mode	Screwed
-------------	---------

#### Electric current

Rated current	160 A
---------------	-------

#### Cover, door

Material thickness cover	2 mm
Door locking	with special tool
Door leave	without
Transparent cover or door	no

#### Materials

Material	Copper
----------	--------

#### Dimensions

Depth of installed product	5 mm
Internal depth	5 mm
Height of installed product	12 mm
Width of installed product	245 mm
Thickness of sidewall material	2 mm

#### Installation, mounting

Suitable for outdoor use	no
--------------------------	----

#### Accessories included

Mounting plate included	no
-------------------------	----

#### Equipment

Quantity of section in width	1
------------------------------	---

#### Standards

European directive WEEE	not concerned
-------------------------	---------------

#### Safety

IK protection code against mechanical impacts	ohne
Impact strength	nicht schlagfest
Fire resistance	-

UC975