



**Earth rail & brace quadro.sys. L500 mm**

Technische Merkmale

**Architecture**

Fixing mode	Screwed
-------------	---------

**Electric current**

Rated current	160 A
---------------	-------

**Cover, door**

Material thickness cover	2 mm
--------------------------	------

Door locking	with special tool
--------------	-------------------

Door leave	without
------------	---------

Transparent cover or door	no
---------------------------	----

**Materials**

Material	Copper
----------	--------

**Dimensions**

Depth of installed product	5 mm
----------------------------	------

Internal depth	5 mm
----------------	------

Height of installed product	12 mm
-----------------------------	-------

Width of installed product	495 mm
----------------------------	--------

Thickness of sidewall material	2 mm
--------------------------------	------

**Installation, mounting**

Suitable for outdoor use	no
--------------------------	----

**Accessories included**

Mounting accessories type	Other
---------------------------	-------

Mounting plate included	yes
-------------------------	-----

**Equipment**

Quantity of section in width	2
------------------------------	---

**Safety**

IK protection code against mechanical impacts	ohne
---	------

Impact strength	nicht schlagfest
-----------------	------------------

Fire resistance	-
-----------------	---

UC976