



WNC001

**cubyko 2W SW wall M grey**

Product Datasheet

**Architecture**

Type of order	Switch
Type of control unit	single rocker
Number of keys	1
Fixing mode	Screwed

**Controls and indicators**

Indicator lamp	no
----------------	----

**Main electrical features**

Frequency	50/60 Hz
Nominal voltage	250 V

**Capacity**

Number of modules for WA	2
--------------------------	---

**Materials**

RAL colour	RAL 7011 - Iron grey
Colour	complete grey
Material	Mixed materials
Material	polypropylène
Type of surface treatment	mat

**Dimensions**

Depth of installed product	64 mm
Height of installed product	75 mm
Width of installed product	75 mm
Dimensions (LLxwxhh)	76x76x61

**Connection**

Connection cross-sect. rigid cable	mini 2x1 mm <sup>2</sup> - maxi 2x2,5 mm <sup>2</sup>
Type of connection	Quickconnect
Type of contacts	2 way

**Standards**

Approvals	EN 60669-1
-----------	------------

**Safety**

Protection index IP	IP55
IK protection code against mechanical impacts	07

**Identification**

Composition	Complete installation with frame
Range	W.1