



WNC023

cubyko PB 1F control light wall M grey

Product Datasheet

Architecture

Type of order	push button
Type of control unit	Push button
Number of keys	1
Fixing mode	Screwed

Controls and indicators

Indicator lamp	yes
----------------	-----

Main electrical features

Frequency	50/60 Hz
Nominal voltage	250 V

Capacity

Number of modules for WA	2
--------------------------	---

Materials

RAL colour	RAL 7011 - Iron grey
Colour	complete grey
Material	Polypropylen
Material	polypropylène
Type of surface treatment	mat

Dimensions

Depth of installed product	64 mm
Height of installed product	75 mm
Width of installed product	75 mm
Dimensions (LLxwxhh)	76x76x75

Installation, mounting

Fixing type	With screws
-------------	-------------

Connection

Connection cross-sect. rigid cable	mini 2x1 mm ² - maxi 2x2,5 mm ²
Type of connection	Quickconnect
Type of contacts	1NC+1NO

Standards

Approvals	EN 60669-1
-----------	------------

Safety

Protection index IP	IP55
IK protection code against mechanical impacts	07

Use conditions

Operating temperature	-15 ... 30 °C
Storage/transport temperature	-50 ... 50 °C

Identification

Composition	Complete installation with frame
Range	cubyko
