



cubyko 2x hor. sock 2P+E wall M white

Product Datasheet

Architecture

| | |
|--------------|---------|
| Type of pole | 2P+T |
| Fixing mode | Screwed |

Functions

| | |
|----------------------------------|-----|
| Centralized terminal connections | yes |
| Overvoltage protection | no |
| With orientation lighting | no |

Controls and indicators

| | |
|---------------------------|---------|
| Indicator lamp | no |
| With or without indicator | without |

Connectivity

| | |
|--------------------------|----|
| With USB charging socket | no |
|--------------------------|----|

Main electrical features

| | |
|-----------------|----------|
| Frequency | 50/60 Hz |
| Nominal voltage | 250 V |

Capacity

| | |
|--------------------------|---|
| Number of modules for WA | 4 |
|--------------------------|---|

Cover, door

| | |
|---------------|----|
| Interlockable | no |
|---------------|----|

Power supply

| | |
|----------------------|-------------------------|
| Special power supply | No special power supply |
|----------------------|-------------------------|

Materials

| | |
|---------------------------|-----------------------|
| RAL colour | RAL 9010 - Pure white |
| Colour | complete white |
| Material | Polypropylen |
| Surface appearance | satın finish |
| Surface protection | other |
| Type of surface treatment | mat varnish |

Dimensions

| | |
|-----------------------------|----------|
| Depth of installed product | 22,8 mm |
| Height of installed product | 75 mm |
| Width of installed product | 146 mm |
| Dimensions (LLxwxhh) | 76x76x96 |

WNC122B



WNE122B

Installation, mounting

| | |
|---------------|-------------|
| Fixing type | With screws |
| Mounting type | surface |

Connection

| | |
|------------------------------------|---|
| Connection cross-sect. rigid cable | mini 2x1 mm ² - maxi 2x2,5 mm ² |
| Type of connection | Quickconnect |
| Phase pickup | L1 |

Accessories included

| | |
|---------------------|----|
| With miniature fuse | no |
|---------------------|----|

Equipment

| | |
|---------------|----|
| On/Off switch | no |
|---------------|----|

Standards

| | |
|-----------|-----------|
| Approvals | NFC 61314 |
|-----------|-----------|

Safety

| | |
|---|------|
| Protection index IP | IP55 |
| IK protection code against mechanical impacts | 07 |

Use conditions

| | |
|-------------------------------|---------------|
| Operating temperature | -15 ... 30 °C |
| Storage/transport temperature | -50 ... 50 °C |

Identification

| | |
|-------|--------|
| Range | cubyko |
|-------|--------|