



**cubyko 3x hor. sock 2P+E wall M grey**

Product Datasheet

**Architecture**

Type of pole	2P+T
Fixing mode	Screwed

**Functions**

Centralized terminal connections	yes
Overvoltage protection	no
With orientation lighting	no

**Controls and indicators**

Indicator lamp	no
With or without indicator	without

**Connectivity**

With USB charging socket	no
--------------------------	----

**Main electrical features**

Frequency	50/60 Hz
Nominal voltage	250 V

**Capacity**

Number of modules for WA	6
--------------------------	---

**Cover, door**

Interlockable	no
---------------	----

**Power supply**

Special power supply	No special power supply
----------------------	-------------------------

**Materials**

RAL colour	RAL 7011 - Iron grey
Colour	complete grey
Material	Polypropylen
Surface appearance	satin finish
Surface protection	other
Type of surface treatment	mat varnish

**Dimensions**

Depth of installed product	42,5 mm
Height of installed product	45 mm
Width of installed product	135 mm
Dimensions (LLxwxhh)	76x76x97

WNC123

**Installation, mounting**

Fixing type	With screws
Mounting type	surface

**Connection**

Connection cross-sect. rigid cable	mini 2x1 mm <sup>2</sup> - maxi 2x2,5 mm <sup>2</sup>
Type of connection	Quickconnect
Phase pickup	L1

**Accessories included**

With miniature fuse	no
---------------------	----

**Equipment**

On/Off switch	no
---------------	----

**Standards**

Approvals	NFC 61314
-----------	-----------

**Safety**

Protection index IP	IP55
IK protection code against mechanical impacts	07

**Use conditions**

Operating temperature	-15 ... 30 °C
Storage/transport temperature	-50 ... 50 °C

**Identification**

Range	cubyko
-------	--------