



WNC025

**cubyko PB 1F w. FPL wall M grey**

Product Datasheet

**Architecture**

|                      |             |
|----------------------|-------------|
| Type of order        | push button |
| Type of control unit | Push button |
| Number of keys       | 1           |
| Fixing mode          | Screwed     |

**Controls and indicators**

|                |     |
|----------------|-----|
| Indicator lamp | yes |
|----------------|-----|

**Main electrical features**

|                 |          |
|-----------------|----------|
| Frequency       | 50/60 Hz |
| Nominal voltage | 24V      |

**Capacity**

|                          |   |
|--------------------------|---|
| Number of modules for WA | 2 |
|--------------------------|---|

**Materials**

|                           |                      |
|---------------------------|----------------------|
| RAL colour                | RAL 7011 - Iron grey |
| Colour                    | complete grey        |
| Material                  | Polypropylen         |
| Material                  | polypropylène        |
| Type of surface treatment | mat                  |

**Dimensions**

|                             |          |
|-----------------------------|----------|
| Depth of installed product  | 64 mm    |
| Height of installed product | 75 mm    |
| Width of installed product  | 75 mm    |
| Dimensions (LLxwxhh)        | 76x76x77 |

**Installation, mounting**

|             |             |
|-------------|-------------|
| Fixing type | With screws |
|-------------|-------------|

**Connection**

|                                    |   |
|------------------------------------|---|
| Connection cross-sect. rigid cable | mini 2x1 mm <sup>2</sup> - maxi 2x2,5 mm <sup>2</sup> |
| Type of connection                 | Quickconnect  |
| Type of contacts                   | 1NC+1NO   |

**Standards**

|           |            |
|-----------|------------|
| Approvals | EN 60669-1 |
|-----------|------------|

**Safety**

|   |      |
|---|------|
| Protection index IP                           | IP55 |
| IK protection code against mechanical impacts | 07   |

**Use conditions**

---

|                               |               |
|-------------------------------|---------------|
| Operating temperature         | -15 ... 30 °C |
| Storage/transport temperature | -50 ... 50 °C |

---

**Identification**

---

|             |                                  |
|-------------|----------------------------------|
| Composition | Complete installation with frame |
| Range       | cubyko                           |

---