



cubyko 3x hor. sock 2P+E wall M white

Product Datasheet

Architecture

Type of pole	2P+T
Fixing mode	Screwed

Functions

Centralized terminal connections	yes
Overvoltage protection	no
With orientation lighting	no

Controls and indicators

Indicator lamp	no
With or without indicator	without

Connectivity

With USB charging socket	no
--------------------------	----

Main electrical features

Frequency	50/60 Hz
Nominal voltage	250 V

Capacity

Number of modules for WA	6
--------------------------	---

Cover, door

Interlockable	no
---------------	----

Power supply

Special power supply	No special power supply
----------------------	-------------------------

Materials

RAL colour	RAL 9010 - Pure white
Colour	complete white
Material	Polypropylen
Surface appearance	satın finish
Surface protection	other
Type of surface treatment	mat varnish

Dimensions

Depth of installed product	22,8 mm
Height of installed product	75 mm
Width of installed product	225 mm
Dimensions (LLxwxhh)	76x76x98

WNC123B

Installation, mounting

Fixing type	With screws
Mounting type	surface

Connection

Connection cross-sect. rigid cable	mini 2x1 mm ² - maxi 2x2,5 mm ²
Type of connection	Quickconnect
Phase pickup	L1

Accessories included

With miniature fuse	no
---------------------	----

Equipment

On/Off switch	no
---------------	----

Standards

Approvals	NFC 61314
-----------	-----------

Safety

Protection index IP	IP55
IK protection code against mechanical impacts	07

Use conditions

Operating temperature	-15 ... 30 °C
Storage/transport temperature	-50 ... 50 °C

Identification

Range	cubyko
-------	--------