



FWB54S

FWB encl., univers, IP44,800x1050x161mm, QC

Product Datasheet

Architecture

Fixing mode flush-mounting/surface-mounting/section make

Functions

With a pipe-in lead yes

Compatibility

Compatible with DIN rail mounting yes

Electric current

Rated current 125 A

Cover, door

Type of door closing Hinged pattern handle and bar locking

Number of keylock of the door 1

Cover type With Notch

Door locking without

Door leave single

Door quantity 2

Cover type Cover

Transparent cover or door no

Materials

Copper weight of the product 0,162 kg

Colour white

RAL colour RAL 9010 - Pure white

Material sheet steel

Dimensions

Depth of installed product 161 mm

Internal depth 161 mm

Height of installed product 800 mm

Width of installed product 1050 mm

Width in division units 12

Thickness of sidewall material 2 mm

Installation, mounting

Suitable for outdoor use no

Connection

Number of conduit inlets 16

Accessories included

Mounting plate included	no
With lock	no

Equipment

Number of rows	20
Quantity of section in width	4
Number of keys	1
Quantity of rails	20
Can be accessorized	yes
Number of openings for flange plates	8
Extension possible	yes

Standards

European directive WEEE	concerned
Protection class according to IEC-61140	II

Safety

IK protection code against mechanical impacts	09
Protection index IP	IP44
Protection class	isol.class II
Impact strength	IK09