



FWB71S

FWB encl., univers, IP44, 1100x300x161mm, QC

Product Datasheet

Architecture

Fixing mode	flush-mounting/surface-mounting/section make
-------------	--

Functions

With a pipe-in lead	yes
---------------------	-----

Configuration

Module	with terminals
--------	----------------

Compatibility

Compatible with DIN rail mounting	yes
-----------------------------------	-----

Electric current

Rated current	125 A
---------------	-------

Cover, door

Type of door closing	hinged pattern handle
Number of keylock of the door	1
Cover type	With Notch
Door locking	without
Door leave	single
Door quantity	1
Cover type	Door
Transparent cover or door	no

Materials

Copper weight of the product	0,042 kg
Colour	white
RAL colour	RAL 9010 - Pure white
Material	sheet steel

Dimensions

Depth of installed product	165 mm
Internal depth	156 mm
Height of installed product	1100 mm
Installation height	1100 mm
Width of installed product	300 mm
Width in division units	12
Thickness of sidewall material	2 mm

Installation, mounting

Suitable for outdoor use	no
--------------------------	----

Connection

Number of conduit inlets	4
--------------------------	---

Accessories included

Mounting plate included	no
With lock	no

Equipment

Number of rows	7
Quantity of section in width	1
Number of keys	1
Quantity of rails	7
Can be accessorized	yes
Number of openings for flange plates	2
Extension possible	yes

Standards

European directive WEEE	concerned
Protection class according to IEC-61140	II

Safety

IK protection code against mechanical impacts	09
Protection index IP	IP44
Protection class	isol.class II
Impact strength	IK09