



FWB32GS

FWB encl., univers, IP44,500x550x161, QC

Product Datasheet

Architecture

Fixing mode flush-mounting/surface-mounting/section make

Configuration

Module with terminals

Compatibility

Compatible with DIN rail mounting yes

Electric current

Rated current 125 A

Cover, door

Type of door closing hinged pattern handle

Number of keylock of the door 1

Cover type With Notch

Door leave single

Door quantity 1

Cover type Door

Transparent cover or door yes

Materials

Colour white

RAL colour RAL 9010 - Pure white

Material Steel

Dimensions

Depth of installed product 165 mm

Internal depth 156 mm

Height of installed product 500 mm

Installation height 500 mm

Width of installed product 550 mm

Width in division units 12

Installation, mounting

Suitable for outdoor use no

Accessories included

Mounting plate included no

With lock no

Equipment

Number of rows	6
Quantity of section in width	2
Number of keys	1
Can be accessorized	yes
Extension possible	yes

Standards

European directive WEEE	concerned
-------------------------	-----------

Safety

Protection index IP	IP44
Protection class	isol.class II