

**FWB encl., univers, IP44,500x1050x161, QC**

Product Datasheet

**Architecture**

Fixing mode	surface-mounting
-------------	------------------

**Configuration**

Module	with terminals
--------	----------------

**Compatibility**

Compatible with DIN rail mounting	yes
-----------------------------------	-----

**Electric current**

Rated current	125 A
---------------	-------

**Cover, door**

Type of door closing	hinged pattern handle
Number of keylock of the door	1
Cover type	Closed (plain)
Door leave	double asymmetric
Door quantity	2
Cover type	Door
Transparent cover or door	yes

**Materials**

Colour	white
RAL colour	RAL 9010 - Pure white
Material	Steel
Type of surface treatment	powder-coated

**Dimensions**

Depth of installed product	165 mm
Internal depth	156 mm
Height of installed product	500 mm
Installation height	500 mm
Width of installed product	1050 mm
Width in division units	12
Thickness of sidewall material	1 mm

**Installation, mounting**

Suitable for outdoor use	no
--------------------------	----

**Connection**

Number of conduit inlets	16
--------------------------	----

## Accessories included

Mounting plate included	no
With lock	no

## Equipment

Number of rows	12
Quantity of section in width	4
Number of keys	1
Quantity of rails	12
Can be accessorized	yes
Number of openings for flange plates	8
Extension possible	yes

## Standards

European directive WEEE	concerned
-------------------------	-----------

## Safety

IK protection code against mechanical impacts	IK07
Protection index IP	IP44
Protection class	isol.class II