



FWB43GS

FWB encl., univers, IP44,650x800xx161, QC

Product Datasheet

Architecture

Fixing mode surface-mounting

Electric current

Rated current 125 A

Cover, door

Type of door closing hinged pattern handle

Number of keylock of the door 1

Cover type With Notch

Door leave double asymmetric

Door quantity 2

Cover type Door

Transparent cover or door yes

Materials

Colour white

RAL colour RAL 9010 - Pure white

Material Steel

Type of surface treatment powder-coated

Dimensions

Depth of installed product 161 mm

Internal depth 161 mm

Height of installed product 650 mm

Width of installed product 800 mm

Width in division units 12

Thickness of sidewall material 1 mm

Installation, mounting

Suitable for outdoor use no

Connection

Number of conduit inlets 12

Accessories included

Mounting plate included no

With lock no

Equipment

Number of rows 12

Quantity of section in width 3

Quantity of rails 12

Number of openings for flange plates 6

Standards

European directive WEEE	concerned
-------------------------	-----------

Safety

IK protection code against mechanical impacts	IK07
-----------------------------------------------	------

Protection index IP	IP44
---------------------	------

Protection class	isol.class II
------------------	---------------
