



FWB63GS

**FWB encl., univers, IP44,950x800xx161, QC**

Product Datasheet

**Architecture**

Fixing mode surface-mounting

**Electric current**

Rated current 125 A

**Cover, door**

Type of door closing hinged pattern handle

Number of keylock of the door 1

Cover type With Notch

Door leave double asymmetric

Door quantity 2

Cover type Door

Transparent cover or door yes

**Materials**

Colour white

RAL colour RAL 9010 - Pure white

Material Steel

Type of surface treatment powder-coated

**Dimensions**

Depth of installed product 161 mm

Internal depth 161 mm

Height of installed product 950 mm

Width of installed product 800 mm

Width in division units 12

Thickness of sidewall material 1 mm

**Installation, mounting**

Suitable for outdoor use no

**Connection**

Number of conduit inlets 12

**Accessories included**

Mounting plate included no

With lock no

**Equipment**

Number of rows 18

Quantity of section in width 3

Number of keys 1

Quantity of rails 18

Number of openings for flange plates 6

**Standards**

---

European directive WEEE	concerned
-------------------------	-----------

---

**Safety**

---

IK protection code against mechanical impacts	IK07
---	------

---

Protection index IP	IP44
---------------------	------

---

Protection class	isol.class II
------------------	---------------

---