



FL552A

Steel inner do., Orion+, 650x500 mm

Product Datasheet

Architecture

Fixing mode Screw mounting

Cover, door

Door type for switch gear cabinet Inner door

Materials

RAL colour RAL 7035 - Light grey

Colour zinc optics

Material Steel

Type of surface treatment untreated

Dimensions

Depth of installed product 20 mm

Height of installed product 600 mm

Width of installed product 450 mm

Standards

Approvals CE

European directive WEEE not concerned

Safety

Protection class isol.class I

Protection index IP IP30

Identification

Range name orion plus