



FL601E

Steel inner door Orion.Plus 750x750 mm

Product Datasheet

Configuration

Version as door for disconnecting switch interlocking	yes
---	-----

Cover, door

Type of door closing	Double lock bar 3mm
Door type for switch gear cabinet	Inner door
Door quantity	1
Transparent cover or door	no

Materials

Colour	RAL 7035
Colour	light grey
RAL colour	RAL 7035 - Light grey
Material	metal
Type of surface treatment	Sendzimir galvanized

Dimensions

Depth of installed product	20 mm
Height of installed product	750 mm
Width of installed product	750 mm

Equipment

Number of keys	2
EMC-version	yes

Standards

European directive WEEE	not concerned
-------------------------	---------------

Safety

Protection index IP	IP30
Protection class	isol.class I