



FL649A

Poly. inner do. Orion+ 800x600 mm

Product Datasheet

Architecture

Fixing mode Screw mounting

Cover, door

Door type for switch gear cabinet Inner door

Materials

RAL colour RAL 7035 - Light grey

Colour light grey

Material glas reinforced polyester

Surface appearance matt

Type of surface treatment untreated

Dimensions

Depth of installed product 20 mm

Height of installed product 750 mm

Width of installed product 550 mm

Standards

Approvals CE

European directive WEEE not concerned

Safety

Protection class isol.class II

Protection index IP IP30

Halogen free yes

Identification

Range name orion plus