



HZC311

Auxiliary contact 1C+1O LBS 20-160A

Product Datasheet

Architecture

Fixing mode Side mounting

Main electrical features

Frequency 50 Hz

Connection

Connection cross-sect. flexible conductor 2,5mm²

Connection cross-sect. rigid cable 2,5mm²

Type of connection with screw

Equipment

Number of auxiliary contacts as normally closed contact 1

Number of auxiliary contacts as normally open contact 1

Standards

European directive WEEE concerned

Use conditions

Operating temperature -20...70 °C

Storage/transport temperature -40...65 °C