



HZC312

Auxiliary contact 2C LBS 20-160A

Product Datasheet

Architecture

Fixing mode	Side mounting
-------------	---------------

Main electrical features

Frequency	50 Hz
-----------	-------

Connection

Connection cross-sect. flexible conductor	2,5mm ²
Connection cross-sect. rigid cable	2,5mm ²
Type of connection	with screw

Equipment

Number of auxiliary contacts as normally open contact	2
---	---

Standards

European directive WEEE	concerned
-------------------------	-----------

Use conditions

Operating temperature	-20...70 °C
Storage/transport temperature	-40...65 °C