



HIM302

## Modular change-over switch 3x20A

Product Datasheet

### Architecture

Type of order	Short thumb-grip
Number of poles	3 P
Type of pole	3 P
Type of case	Fixed built-in

### Functions

Reversing switch	yes
------------------	-----

### Controls and indicators

Motor drive integrated	no
------------------------	----

### Main electrical features

Rated operational voltage Ue	380 / 415 V
Frequency	50/60 Hz

### Electric current

Rated current	20 A
Short-circuit current with gl-gG fuses	50 kA
Rated short-time withstand current 1s	1,26 kA
Rated operational current in AC23 category A	20 A

### Power

Total power loss under IN	1,2 W
Power loss per pole at In	0,4 W
Contact rating with 400 V in AC1	13 kW

### Cover, door

Interlockable	yes
---------------	-----

### Connection

Type of connection	with screw
--------------------	------------

### Equipment

Motor drive optional	no
----------------------	----

### Standards

Standard text	IEC 60947-3
European directive WEEE	concerned

### Safety

Protection index IP	IP20
---------------------	------

**Use conditions**

Operating temperature	-20...70 °C
Air humidity protection	yes according to IEC 68-2-30