



SVN321

Impulse 1NC Pushbutton

Product Datasheet

Main electrical features

Rated operational voltage Ue	230 V
Frequency	50/60 Hz

Voltage

Rated insulation voltage	250 V
Rated impulse withstand voltage	4000 V
Switching voltage	230 V

Electric current

Rated current	16 A
Momentary-contact current	16 A
Prospective short circuit withstand with MCB 16A B curve	1000A [Prot:16AcurveB]
Prospective short circuit withstand with fuse 16A gG	1000A [Prot:16AgG]
Thermal rated current outside of housings	16 A

Endurance

Electric endurance in number of cycles	15000
Number of mechanical operations	15000

Materials

Colour	not applicable
--------	----------------

Dimensions

Depth of installed product	66 mm
Height of installed product	83 mm
Width of installed product	17,5 mm

Installation, mounting

Tightening torque	1,7Nm
-------------------	-------

Connection

Connection cross-sect. flexible conductor	0,75 / 6mm ²
Connection cross-sect. rigid cable	0,75 / 10mm ²
Type of connection	with screw

Equipment

Quantity of NC contacts	1
-------------------------	---

Standards

European directive WEEE	concerned
-------------------------	-----------

Safety

Protection index IP	IP20
---------------------	------

Use conditions

Operating temperature	-20...50 °C
Degree of pollution according to IEC 60664 / IEC 60947-2	3
Altitude	2000 m
Storage/transport temperature	-40...80 °C