



ATA163058014

**Flat corner, ATEHA, 16x30, brown**

Product Datasheet

**Architecture**

Fixing mode	Clipped
-------------	---------

**Functions**

Overlapping	yes
Suitable for functional integrity according to DIN 4102-12	no

**Configuration**

Antibacterial treatment	no
Symetrical	yes

**Cover, door**

Lid with softlip	No
------------------	----

**Materials**

Colour	brown
RAL colour	RAL 8014 - Sepia brown
Material	ABS
Type of surface treatment	untreated

**Dimensions**

Trunking height	16 mm
Length	58 mm
Trunking width	30 mm

**Installation, mounting**

Base punching	Without base punching
---------------	-----------------------

**Settings**

Angle range	90 °
-------------	------

**Accessories included**

Accessory configuration	Moulded
-------------------------	---------

**Equipment**

With protective film	no
----------------------	----

**Standards**

Approvals	EN50085-2-1
-----------	-------------

**Safety**

Protection index IP	IP40
Halogen free	yes
Impact strength	IK07

**Use conditions**

Operating temperature	-5...60 °C
-----------------------	------------

**temperatur**

Ambient temperature	-5...60 °C
---------------------	------------