



ATA125068014

End cap, ATEHA, 12x50, brown

Product Datasheet

Architecture

Fixing mode	Clipped
-------------	---------

Functions

Overlapping	yes
Suitable for functional integrity according to DIN 4102-12	no

Configuration

Antibacterial treatment	no
-------------------------	----

Connectivity

Trunking coupling	without coupler
-------------------	-----------------

Materials

Colour	brown
RAL colour	RAL 8014 - Sepia brown
Material	ABS
Material group	plastic
Type of surface treatment	untreated

Dimensions

Trunking height	12 mm
Trunking width	50 mm

Equipment

With protective film	no
----------------------	----

Standards

Approvals	EN50085-2-1
European directive RoHs	voluntary compliance

Safety

Protection index IP	IP40
Halogen free	yes
Impact strength	IK07

Use conditions

Operating temperature	-5...60 °C
-----------------------	------------

temperatur

Ambient temperature	-5...60 °C
---------------------	------------