



ATA205019010



Trunking 20x50, L=2,0m, pure white

Product Datasheet

Architecture

Fixing mode	bottom punched
-------------	----------------

Functions

Suitable for functional integrity according to DIN 4102-12	no
--	----

Configuration

Antibacterial treatment	no
-------------------------	----

Connectivity

Trunking coupling	without coupler
-------------------	-----------------

Capacity

Maximum number of cables (Ø 11 mm, 50% fill)	4
Maximum number of cables (Ø 11 mm, 50% fill)	5

Cover, door

Lid shape	premounted
-----------	------------

Materials

Colour	pure white
RAL colour	RAL 9010 - Pure white
Material	PVC
Material group	plastic
Type of surface treatment	untreated
Transparent	no

Dimensions

Trunking height	20 mm
Length	2000 mm
Trunking width	52 mm

Installation, mounting

Base punching	Without base punching
---------------	-----------------------

Cable

Number of wires 1,5 mm ² - 40% filling degree	65
Internal/useful cross section	900 mm ²
Number of wires 2,5 mm ² - 40% filling degree	48

Scope of delivery

Delivery on roll	no
------------------	----

Equipment

Number of fix dividers	1
Compartment quantity	2
Cable retainers per meter	2
Cable fixing clips included	yes
With protective film	no

Standards

Approvals	EN50085-2-1
European directive RoHs	voluntary compliance

Safety

Protection index IP	IP40
Halogen free	no
Impact strength	IK07

Use conditions

Operating temperature	-5...65 °C
-----------------------	------------